

Blacksmith Wave

Order Sheet | Ti-Base

- Customer Name : _____
- Contact Number : _____
- Address : _____
- Business Name : _____
- E-mail (For Invoicing) : _____

No.	Product	REF	Display Name	MSRP	QTY
1	Ti-Base	TBDNR4513H	Ti-BASE Compatible with Dentium SuperLine Hex (C=1mm, P=3mm)	40	
2	Ti-Base	TBDNR4515H	Ti-BASE Compatible with Dentium SuperLine Hex (C=1mm, P=5mm)	40	
3	Ti-Base	TBDNR4523H	Ti-BASE Compatible with Dentium SuperLine Hex (C=2mm, P=3mm)	40	
4	Ti-Base	TBDNR4525H	Ti-BASE Compatible with Dentium SuperLine Hex (C=2mm, P=5mm)	40	
5	Ti-Base	TBDNR4513N	Ti-BASE Compatible with Dentium SuperLine Non-Engaging (C=1mm, P=3mm)	40	
6	Ti-Base	TBDNR4515N	Ti-BASE Compatible with Dentium SuperLine Non-Engaging (C=1mm, P=5mm)	40	
7	Ti-Base	TBDNR4523N	Ti-BASE Compatible with Dentium SuperLine Non-Engaging (C=2mm, P=3mm)	40	
8	Ti-Base	TBDNR4525N	Ti-BASE Compatible with Dentium SuperLine Non-Engaging (C=2mm, P=5mm)	40	
9	Ti-Base	TBMEM4313H	Ti-BASE Compatible with Megagen AnyRidge Hex (C=1mm, P=3mm)	40	
10	Ti-Base	TBMEM4315H	Ti-BASE Compatible with Megagen AnyRidge Hex (C=1mm, P=5mm)	40	
11	Ti-Base	TBMEM4323H	Ti-BASE Compatible with Megagen AnyRidge Hex (C=2mm, P=3mm)	40	
12	Ti-Base	TBMEM4325H	Ti-BASE Compatible with Megagen AnyRidge Hex (C=2mm, P=5mm)	40	
13	Ti-Base	TBMEM4313N	Ti-BASE Compatible with Megagen AnyRidge Non-Engaging (C=1mm, P=3mm)	40	
14	Ti-Base	TBMEM4315N	Ti-BASE Compatible with Megagen AnyRidge Non-Engaging (C=1mm, P=5mm)	40	
15	Ti-Base	TBMEM4323N	Ti-BASE Compatible with Megagen AnyRidge Non-Engaging (C=2mm, P=3mm)	40	
16	Ti-Base	TBMEM4325N	Ti-BASE Compatible with Megagen AnyRidge Non-Engaging (C=2mm, P=5mm)	40	
17	Ti-Base	TBNO3513N	Ti-BASE Compatible with Nobel Active 3.0 Non-Engaging (C=1mm, P=3mm)	40	
18	Ti-Base	TBNO3515N	Ti-BASE Compatible with Nobel Active 3.0 Non-Engaging (C=1mm, P=5mm)	40	
19	Ti-Base	TBNO3523N	Ti-BASE Compatible with Nobel Active 3.0 Non-Engaging (C=2mm, P=3mm)	40	
20	Ti-Base	TBNO3525N	Ti-BASE Compatible with Nobel Active 3.0 Non-Engaging (C=2mm, P=5mm)	40	
21	Ti-Base	TBNO3513T	Ti-BASE Compatible with Nobel Active 3.0 Torx (C=1mm, P=3mm)	40	
22	Ti-Base	TBNO3515T	Ti-BASE Compatible with Nobel Active 3.0 Torx (C=1mm, P=5mm)	40	
23	Ti-Base	TBNO3523T	Ti-BASE Compatible with Nobel Active 3.0 Torx (C=2mm, P=3mm)	40	
24	Ti-Base	TBNO3525T	Ti-BASE Compatible with Nobel Active 3.0 Torx (C=2mm, P=5mm)	40	
25	Ti-Base	TBNO4013H	Ti-BASE Compatible with Nobel Active NP Hex (C=1mm, P=3mm)	40	
26	Ti-Base	TBNO4015H	Ti-BASE Compatible with Nobel Active NP Hex (C=1mm, P=5mm)	40	

Blacksmith Wave

Order Sheet | Ti-Base

- Customer Name : _____
- Contact Number : _____
- Address : _____
- Business Name : _____
- E-mail (For Invoicing) : _____

No.	Product	REF	Display Name	MSRP	QTY
27	Ti-Base	TBNO4023H	Ti-BASE Compatible with Nobel Active NP Hex (C=2mm, P=3mm)	40	
28	Ti-Base	TBNO4025H	Ti-BASE Compatible with Nobel Active NP Hex (C=2mm, P=5mm)	40	
29	Ti-Base	TBNO4013N	Ti-BASE Compatible with Nobel Active NP Non-Engaging (C=1mm, P=3mm)	40	
30	Ti-Base	TBNO4015N	Ti-BASE Compatible with Nobel Active NP Non-Engaging (C=1mm, P=5mm)	40	
31	Ti-Base	TBNO4023N	Ti-BASE Compatible with Nobel Active NP Non-Engaging (C=2mm, P=3mm)	40	
32	Ti-Base	TBNO4025N	Ti-BASE Compatible with Nobel Active NP Non-Engaging (C=2mm, P=5mm)	40	
33	Ti-Base	TBNO4513H	Ti-BASE Compatible with Nobel Active RP Hex (C=1mm, P=3mm)	40	
34	Ti-Base	TBNO4515H	Ti-BASE Compatible with Nobel Active RP Hex (C=1mm, P=5mm)	40	
35	Ti-Base	TBNO4523H	Ti-BASE Compatible with Nobel Active RP Hex (C=2mm, P=3mm)	40	
36	Ti-Base	TBNO4525H	Ti-BASE Compatible with Nobel Active RP Hex (C=2mm, P=5mm)	40	
37	Ti-Base	TBNO4513N	Ti-BASE Compatible with Nobel Active RP Non-Engaging (C=1mm, P=3mm)	40	
38	Ti-Base	TBNO4515N	Ti-BASE Compatible with Nobel Active RP Non-Engaging (C=1mm, P=5mm)	40	
39	Ti-Base	TBNO4523N	Ti-BASE Compatible with Nobel Active RP Non-Engaging (C=2mm, P=3mm)	40	
40	Ti-Base	TBNO4525N	Ti-BASE Compatible with Nobel Active RP Non-Engaging (C=2mm, P=5mm)	40	
41	Ti-Base	TBNO5013H	Ti-BASE Compatible with Nobel Active WP Hex (C=1mm, P=3mm)	40	
42	Ti-Base	TBNO5015H	Ti-BASE Compatible with Nobel Active WP Hex (C=1mm, P=5mm)	40	
43	Ti-Base	TBNO5023H	Ti-BASE Compatible with Nobel Active WP Hex (C=2mm, P=3mm)	40	
44	Ti-Base	TBNO5025H	Ti-BASE Compatible with Nobel Active WP Hex (C=2mm, P=5mm)	40	
45	Ti-Base	TBNO5013N	Ti-BASE Compatible with Nobel Active WP Non-Engaging (C=1mm, P=3mm)	40	
46	Ti-Base	TBNO5015N	Ti-BASE Compatible with Nobel Active WP Non-Engaging (C=1mm, P=5mm)	40	
47	Ti-Base	TBNO5023N	Ti-BASE Compatible with Nobel Active WP Non-Engaging (C=2mm, P=3mm)	40	
48	Ti-Base	TBNO5025N	Ti-BASE Compatible with Nobel Active WP Non-Engaging (C=2mm, P=5mm)	40	
49	Ti-Base	TBOSM4013H	Ti-BASE Compatible with Osstem TS Mini Hex (C=1mm, P=3mm)	40	
50	Ti-Base	TBOSM4015H	Ti-BASE Compatible with Osstem TS Mini Hex (C=1mm, P=5mm)	40	
51	Ti-Base	TBOSM4023H	Ti-BASE Compatible with Osstem TS Mini Hex (C=2mm, P=3mm)	40	
52	Ti-Base	TBOSM4025H	Ti-BASE Compatible with Osstem TS Mini Hex (C=2mm, P=5mm)	40	

Blacksmith Wave

Order Sheet | Ti-Base

- Customer Name : _____
- Contact Number : _____
- Address : _____
- Business Name : _____
- E-mail (For Invoicing) : _____

No.	Product	REF	Display Name	MSRP	QTY
53	Ti-Base	TBOSM4013N	Ti-BASE Compatible with Osstem TS Mini Non-Engaging (C=1mm, P=3mm)	40	
54	Ti-Base	TBOSM4015N	Ti-BASE Compatible with Osstem TS Mini Non-Engaging (C=1mm, P=5mm)	40	
55	Ti-Base	TBOSM4023N	Ti-BASE Compatible with Osstem TS Mini Non-Engaging (C=2mm, P=3mm)	40	
56	Ti-Base	TBOSM4025N	Ti-BASE Compatible with Osstem TS Mini Non-Engaging (C=2mm, P=5mm)	40	
57	Ti-Base	TBOSR4513H	Ti-BASE Compatible with Osstem TS Regular Hex (C=1mm, P=3mm)	40	
58	Ti-Base	TBOSR4515H	Ti-BASE Compatible with Osstem TS Regular Hex (C=1mm, P=5mm)	40	
59	Ti-Base	TBOSR4523H	Ti-BASE Compatible with Osstem TS Regular Hex (C=2mm, P=3mm)	40	
60	Ti-Base	TBOSR4525H	Ti-BASE Compatible with Osstem TS Regular Hex (C=2mm, P=5mm)	40	
61	Ti-Base	TBOSR4513N	Ti-BASE Compatible with Osstem TS Regular Non-Engaging (C=1mm, P=3mm)	40	
62	Ti-Base	TBOSR4515N	Ti-BASE Compatible with Osstem TS Regular Non-Engaging (C=1mm, P=5mm)	40	
63	Ti-Base	TBOSR4523N	Ti-BASE Compatible with Osstem TS Regular Non-Engaging (C=2mm, P=3mm)	40	
64	Ti-Base	TBOSR4525N	Ti-BASE Compatible with Osstem TS Regular Non-Engaging (C=2mm, P=5mm)	40	
65	Ti-Base	TBSTN3813N	Ti-BASE Compatible with Straumann BL NC Non-Engaging (C=1mm, P=3mm)	40	
66	Ti-Base	TBSTN3815N	Ti-BASE Compatible with Straumann BL NC Non-Engaging (C=1mm, P=5mm)	40	
67	Ti-Base	TBSTN3823N	Ti-BASE Compatible with Straumann BL NC Non-Engaging (C=2mm, P=3mm)	40	
68	Ti-Base	TBSTN3825N	Ti-BASE Compatible with Straumann BL NC Non-Engaging (C=2mm, P=5mm)	40	
69	Ti-Base	TBSTN3813S	Ti-BASE Compatible with Straumann BL NC Square (C=1mm, P=3mm)	40	
70	Ti-Base	TBSTN3815S	Ti-BASE Compatible with Straumann BL NC Square (C=1mm, P=5mm)	40	
71	Ti-Base	TBSTN3823S	Ti-BASE Compatible with Straumann BL NC Square (C=2mm, P=3mm)	40	
72	Ti-Base	TBSTN3825S	Ti-BASE Compatible with Straumann BL NC Square (C=2mm, P=5mm)	40	
73	Ti-Base	TBSTR4013N	Ti-BASE Compatible with Straumann BL RC Non-Engaging (C=1mm, P=3mm)	40	
74	Ti-Base	TBSTR4015N	Ti-BASE Compatible with Straumann BL RC Non-Engaging (C=1mm, P=5mm)	40	
75	Ti-Base	TBSTR4023N	Ti-BASE Compatible with Straumann BL RC Non-Engaging (C=2mm, P=3mm)	40	
76	Ti-Base	TBSTR4025N	Ti-BASE Compatible with Straumann BL RC Non-Engaging (C=2mm, P=5mm)	40	
77	Ti-Base	TBSTR4013S	Ti-BASE Compatible with Straumann BL RC Square (C=1mm, P=3mm)	40	
78	Ti-Base	TBSTR4015S	Ti-BASE Compatible with Straumann BL RC Square (C=1mm, P=5mm)	40	

Blacksmith Wave

Order Sheet | Ti-Base

- Customer Name : _____
- Contact Number : _____
- Address : _____
- Business Name : _____
- E-mail (For Invoicing) : _____

No.	Product	REF	Display Name	MSRP	QTY
79	Ti-Base	TBSTR4023S	Ti-BASE Compatible with Straumann BL RC Square (C=2mm, P=3mm)	40	
80	Ti-Base	TBSTR4025S	Ti-BASE Compatible with Straumann BL RC Square (C=2mm, P=5mm)	40	
81	Ti-Base	TBZM3813H	Ti-BASE Compatible with Zimmer TSV 3.5 Hex (C=1mm, P=3mm)	40	
82	Ti-Base	TBZM3815H	Ti-BASE Compatible with Zimmer TSV 3.5 Hex (C=1mm, P=5mm)	40	
83	Ti-Base	TBZM3823H	Ti-BASE Compatible with Zimmer TSV 3.5 Hex (C=2mm, P=3mm)	40	
84	Ti-Base	TBZM3825H	Ti-BASE Compatible with Zimmer TSV 3.5 Hex (C=2mm, P=5mm)	40	
85	Ti-Base	TBZM3813N	Ti-BASE Compatible with Zimmer TSV 3.5 Non-Engaging (C=1mm, P=3mm)	40	
86	Ti-Base	TBZM3815N	Ti-BASE Compatible with Zimmer TSV 3.5 Non-Engaging (C=1mm, P=5mm)	40	
87	Ti-Base	TBZM3823N	Ti-BASE Compatible with Zimmer TSV 3.5 Non-Engaging (C=2mm, P=3mm)	40	
88	Ti-Base	TBZM3825N	Ti-BASE Compatible with Zimmer TSV 3.5 Non-Engaging (C=2mm, P=5mm)	40	
89	Ti-Base	TBZM4513H	Ti-BASE Compatible with Zimmer TSV 4.5 Hex (C=1mm, P=3mm)	40	
90	Ti-Base	TBZM4515H	Ti-BASE Compatible with Zimmer TSV 4.5 Hex (C=1mm, P=5mm)	40	
91	Ti-Base	TBZM4523H	Ti-BASE Compatible with Zimmer TSV 4.5 Hex (C=2mm, P=3mm)	40	
92	Ti-Base	TBZM4525H	Ti-BASE Compatible with Zimmer TSV 4.5 Hex (C=2mm, P=5mm)	40	
93	Ti-Base	TBZM4513N	Ti-BASE Compatible with Zimmer TSV 4.5 Non-Engaging (C=1mm, P=3mm)	40	
94	Ti-Base	TBZM4515N	Ti-BASE Compatible with Zimmer TSV 4.5 Non-Engaging (C=1mm, P=5mm)	40	
95	Ti-Base	TBZM4523N	Ti-BASE Compatible with Zimmer TSV 4.5 Non-Engaging (C=2mm, P=3mm)	40	
96	Ti-Base	TBZM4525N	Ti-BASE Compatible with Zimmer TSV 4.5 Non-Engaging (C=2mm, P=5mm)	40	
97	Ti-Base	TBZM6513H	Ti-BASE Compatible with Zimmer TSV 5.7 Hex (C=1mm, P=3mm)	40	
98	Ti-Base	TBZM6515H	Ti-BASE Compatible with Zimmer TSV 5.7 Hex (C=1mm, P=5mm)	40	
99	Ti-Base	TBZM6523H	Ti-BASE Compatible with Zimmer TSV 5.7 Hex (C=2mm, P=3mm)	40	
100	Ti-Base	TBZM6525H	Ti-BASE Compatible with Zimmer TSV 5.7 Hex (C=2mm, P=5mm)	40	
101	Ti-Base	TBZM6513N	Ti-BASE Compatible with Zimmer TSV 5.7 Non-Engaging (C=1mm, P=3mm)	40	
102	Ti-Base	TBZM6515N	Ti-BASE Compatible with Zimmer TSV 5.7 Non-Engaging (C=1mm, P=5mm)	40	
103	Ti-Base	TBZM6523N	Ti-BASE Compatible with Zimmer TSV 5.7 Non-Engaging (C=2mm, P=3mm)	40	
104	Ti-Base	TBZM6525N	Ti-BASE Compatible with Zimmer TSV 5.7 Non-Engaging (C=2mm, P=5mm)	40	